

Ampco Pumps
Company



AC+ DRY BLENDER

INCREASE PRODUCTION AND ACHIEVE
BETTER PRODUCT UNIFORMITY



Fast, consistent blending is now available with the Ampco AC+ Dry Blender series. The AC+ Dry blender is designed to thoroughly and efficiently blend dry ingredients with liquid ingredients. Lumping, foaming and fisheyes are eliminated.

AC+ Dry Blender Design

The AC+ Dry Blender uses the proven design of a tube within a tube and a centrifugal pump, but with the improved shaft and threaded impeller nut construction of the AC+ pump.

The tube within a tube design keeps dry ingredients and liquids separated until they are introduced in the mixing chamber while maximizing induction vacuum. Dry ingredients are introduced without excess air so lumping and foaming do not occur. Fast, uniform and continuous material absorption up to 350lbs/min.

The AC+ Dry blender can be easily integrated into current process systems.

AC+ Blenders are also suitable for liquid to liquid applications.

AC+ Dry Blender Series

- All wetted components are 316L stainless steel.
- Fast, uniform and continuous material absorption up to 350lbs.
- No pre- or post-blending necessary in many operations
- Easy to operate, increased production
- Easily integrated into existing systems
- Savings in product loss and reprocessing time

Applications for the AC+ Dry Blender

- Dairy - powdered milk, butter-milk, ice cream mix, whey protein
- Food - pudding, chip dip, pizza sauce, stabilizer addition, powdered egg, starch and gum
- Beverage - concentrate, flavor addition, vitamin drinks
- Personal Care - soap blends, lotion, cosmetics, hair gel, tooth paste
- Chemical - herbicide agent, film solution, fertilizer, biodiesel
- Pharmaceutical - active ingredient blends, cough syrup, tablet coating



**The AC+ Dry Blender
delivers consistent blending
with every batch.**



MODEL AC+2116



Powder addition rate: up to 50 lbs. per minute (23kg/min)
Normal liquid flow rate: 40 GPM (9.1 m³/hr)
Powder addition inlet: 2 inch
Liquid inlet: 1-1/2 inch
Liquid outlet: 1-1/2 inch
Clamp connection standard
Close coupled to a 5HP, 3600 RPM motor

MODEL AC+2116 SYSTEM



Powder addition rate: up to 50 lbs. per minute (23kg/min)
Normal liquid flow rate: 40 GPM (9.1 m³/hr)
Powder addition inlet: 2 inch
Liquid inlet: 1-1/2 inch (at feed pump)
Liquid outlet: 1-1/2 inch
Clamp connection standard
Close coupled to a 5HP, 3600 RPM motor
Shipped complete with supply pump, control panel and cart

MODEL AC+3218



Powder addition rate: up to 100 lbs. per minute (45kg/min)
Normal liquid flow rate: 110 GPM (25 m³/hr)
Powder addition inlet: 3 inch
Liquid inlet: 1-1/2 inch
Liquid outlet: 2 inch
Clamp connection standard
304 Stainless steel base with belt drive
20HP Motor

MODEL AC+4329



Powder addition rate: up to 350 lbs. per minute (159kg/min)
Normal liquid flow rate: 130 GPM (29.5 m³/hr)
Powder addition inlet: 4 inch
Liquid inlet: 2 inch
Liquid outlet: 4 inch
Clamp connection standard
304 Stainless steel base with belt drive
30HP Motor

