

Alfa Laval DuraCirc

Circumferential Piston Pump

Introduction

The Alfa Laval DuraCirc delivers the perfect balance of durability, reliability, high efficiency and superior hygienic performance. Combined with design features enabling simple service, the DuraCirc keeps process running. In addition to a class leading range of flow and pressure capabilities, DuraCirc comes with globally recognized hygienic certification. The innovative design also includes features that make cleaning and maintenance faster, easier and more dependable.

Applications

Designed for Cleaning-in-Place (CIP), the Alfa Laval DuraCirc is ideal for hygienic applications within the dairy, food, beverage, home and personal care industries. The highly efficient design is particularly suited to applications that are low in viscosity with medium to high discharge pressures and require equipment that can be cleaned in place.

The DuraCirc Circumferential Piston Pump is available with 13 different pump head displacements to handle flow rates up to 656 US gpm and differential pressures up to 40 bar.

Benefits

- DuraCirc Hi-Life rotors provides high efficiency while eliminating contact to casing thus increasing pump life.
- Certified to both EHEDG and 3A, reducing both process cross contamination risk and CIP cycle time, maintaining process yield as well as cutting cleaning costs.
- Truly front-loading single seal, full component interchangeability without complicated maintenance procedures, long life bearing operation and one single long-life lubricant making service faster and easier, increasing process uptime.
- Robust, durable design via strong gearcase incorporating increased diameter shafts and optimally positioned heavy-duty bearings, minimizes risk of pump head contact, reducing service requirement, maintaining process continuity.
- DuraCirc Uni-Fit port option allows easy direct replacement of other major brands into existing process systems, without changing pipework.



Standard design

Twin-wing Hi-Life piston rotors made of special non-galling alloy are standard. All other media contacting steel components, like the rotor case, front cover and rotor nuts are in W. 1.4404 (AISI 316L). With stainless steel gear case and feet, the DuraCirc pump has an all stainless steel exterior, making it exceptional corrosion resistant.

The gearbox is as standard designed with duplex shafts and a strong, long life bearing arrangement. This provides for a very robust and rigid shaft assembly design – a prerequisite for the very high volumetric efficiency achieved.

With profiled defined compression elastomers and an optimised shaft seal location, the DuraCirc is designed according to the most stringent hygienic design standards and with verified and effective CIP cleanability.

The pump features a front-loading single mechanical seal, which allows quick and easy inspection or replacement without the

need to disassemble pipework. Single flushed and double mechanical shaft seals as well as O-ring seals are available as options.

The Alfa Laval DuraCirc can be supplied either as a bare shaft pump or mounted on a base plate complete with coupling, guard, gear motor and shroud for easy, plug-and-play installation.

Working principle

The rotor pistons rotate around the circumference of the channel in the pump casing. This continuously generates a partial

vacuum at the suction port as the rotors unmesh, causing fluid to enter the pump. The fluid is transported around the channel by the rotor pistons, and is displaced as the rotor pistons re-mesh, generating pressure at the discharge port. The direction of flow is reversible.



Authorized to carry the 3A symbol

Technical data

Standard specification

Piston rotors:	DuraCirc Hi-Life, Non-Galling Alloy
Other product wetted steel parts:	W. 1.4404 (316L)
Inside surface finish:	Mech Ra ≤ 0.8
Shafts:	Duplex 1.4460 (329)
Gear box:	Stainless steel
Base plate:	Stainless steel
Coupling guard:	Stainless steel
Product wetted elastomers:	EPDM
Other elastomers:	FPM
Shaft seal:	Single mechanical
Rotary seal face:	Silicon Carbide
Stationary seal face:	Carbon

Shaft seals

Single mechanical, single mechanical with flush, double mechanical and single and flushed O-ring seal available.

Max process pressure, mechanical seal, SiC/Car:	217 PSI
Max process pressure, mechanical seal, SiC/SiC:	Max pressure of pump
Max flush pressure, single flush:	7.25 PSI
Max flush pressure, double mechanical seal, SiC/Car:	232 PSI
Max flush pressure, double mechanical seal, SiC/SiC:	290 PSI
Max process pressure, O-ring seal:	102 PSI
Max flush pressure, O-ring seal:	7.25 PSI
Flush water consumption:	7 gallon/hour
Flush connections, DuraCirc 32-43:	NPT 1/8"
Flush connections, DuraCirc 52-74:	NPT 1/4"

Temperature

Max process and CIP temperature:	302°F
----------------------------------	-------

Motors

Gear motor, 4 poles, to Nema standard, premium efficiency, suitable for frequency conversion.

Warranty

Extended 3-years warranty on DuraCirc pumps. The warranty covers all non wear parts on the condition that genuine Alfa Laval Spare Parts are used.

Process data

Pump Model	Displacement			Inlet/Outlet		Diff. Pressure		Max speed
	Litres/rev	Imp gall/100 rev	US gall/100 rev	mm	inch	Bar	PSI	rpm
32	0,03	0.66	0.79	25	1	25	362	1000
33	0,06	1.32	1.58	40	1½	25	362	1000
34	0,12	2.64	3.17	50	2	16	232	1000
42	0,23	5.06	6.07	50	2	20	290	750
43	0,29	6.38	7.66	50	2	13	188	750
52	0,38	8.36	10.03	50	2	37	536	750

Pump Model	Displacement			Inlet/Outlet		Diff. Pressure		Max speed
	Litres/rev	Imp gal/100 rev	US gal/100 rev	mm	inch	Bar	PSI	rpm
53	0,59	12.97	15.57	65	2½	25	362	750
54	0,96	21.12	25.3	80	3	16	232	750
62	1,44	31.67	38.04	80	3	37	536	600
63	1,97	43.33	52.03	100	4	25	362	600
72	1,92	42.23	50.7	100	4	40	580	600
73	2,86	62.91	75.55	150	6	25	362	600
74	4,14	91.1	109.4	150	6	16	232	600

Dimensions

(inch)




Figure 1. Horizontally ported

ØU = 4 Holes

J = Key Length

K = Key Width

DuraCirc Uni-Fit dimensions

Pump Model	A	B	C	D	E	F	G	HB	HT	J	K	L	M	N	P	Q	R	S	T	U
32	1.0	3.5	4.2	8.3	0.5	0.9	1.7	2.9	5.6	1.3	0.2	13.0	2.0	4.9	3.9	1.0	5.5	5.9	4.9	0.5
33	1.5	3.5	4.2	8.3	0.5	0.9	1.7	2.9	5.6	1.3	0.2	13.2	2.0	4.9	3.9	1.0	5.5	5.9	4.9	0.5
34	1.5	3.5	4.2	8.3	0.5	0.9	1.7	2.9	5.6	1.3	0.2	14.0	2.4	4.9	3.9	1.0	5.5	5.9	4.9	0.5
42	1.5	4.3	5.2	10.3	0.4	1.1	2.2	3.5	6.9	1.6	0.3	16.3	2.8	5.5	4.9	0.6	6.2	7.3	6.0	0.6
43	2.0	4.3	5.2	10.3	0.4	1.1	2.2	3.5	6.9	1.6	0.3	16.6	3.2	5.5	4.9	0.6	6.2	7.3	6.0	0.6
52	2.0	5.4	7.3	13.7	1.6	1.5	2.6	5.1	9.6	2.5	0.4	18.6	3.3	6.6	5.5	0.9	7.1	8.7	7.5	0.6
53	2.5	5.4	7.3	13.7	1.6	1.5	2.6	5.1	9.6	2.5	0.4	19.1	3.5	6.6	5.5	0.9	7.1	8.7	7.5	0.6
54	3.0	5.4	7.3	13.7	1.6	1.5	2.6	5.1	9.6	2.5	0.4	20.2	4.4	6.6	5.5	0.9	7.1	8.7	7.5	0.6
62	3.0	6.3	9.4	17.2	2.3	1.8	3.3	6.4	12.3	2.8	0.6	23.1	4.6	7.8	6.3	1.0	8.8	9.8	8.5	0.6
63	4.0	6.3	9.4	17.2	2.3	1.8	3.3	6.4	12.3	2.8	0.6	23.9	4.9	7.8	6.3	1.0	8.8	9.8	8.5	0.6
72	4.0	7.4	10.4	19.8	1.7	2.4	4.1	6.9	13.9	3.5	0.7	27.6	4.3	9.7	8.5	0.8	10.9	11.0	9.7	0.6
73	6.0	8.0	10.4	19.8	1.7	2.4	4.1	6.9	13.9	3.5	0.7	28.5	4.8	9.7	8.5	0.8	10.9	11.0	9.7	0.6
74	6.0	8.5	10.4	19.8	1.7	2.4	4.1	6.9	13.9	3.5	0.7	29.9	5.7	9.7	8.5	0.8	10.9	11.0	9.7	0.6



Note! DuraCirc Uni-Fit is an option to meet port to port and port height dimensions of other major brands.

DuraCirc standard dimensions

Pump Model	A	B	C	D	E	F	G	HB	HT	J	K	L	M	N	P	Q	R	S	T	U
32	1.0	4.1	4.5	8.7	0.5	0.9	1.7	3.2	5.9	1.3	0.2	13.0	2.0	4.9	3.9	1.0	5.5	5.9	4.9	0.5
33	1.5	4.1	4.5	8.7	0.5	0.9	1.7	3.2	5.9	1.3	0.2	13.2	2.0	4.9	3.9	1.0	5.5	5.9	4.9	0.5
34	2.0	4.1	4.5	8.7	0.5	0.9	1.7	3.2	5.9	1.3	0.2	13.9	2.4	4.9	3.9	1.0	5.5	5.9	4.9	0.5
42	2.0	4.9	5.2	10.3	0.4	1.1	2.2	3.5	6.9	1.6	0.3	16.3	2.8	5.5	4.9	0.6	6.2	7.3	6.1	0.6
43	2.0	4.9	5.2	10.3	0.4	1.1	2.2	3.5	6.9	1.6	0.3	16.6	3.2	5.5	4.9	0.6	6.2	7.3	6.1	0.6
52	2.0	5.9	6.4	12.8	0.7	1.5	2.6	4.2	8.7	2.5	0.4	18.6	3.3	6.6	5.5	0.9	7.1	8.7	7.5	0.6
53	2.5	5.9	6.4	12.8	0.7	1.5	2.6	4.2	8.7	2.5	0.4	19.1	3.5	6.6	5.5	0.9	7.1	8.7	7.5	0.6
54	3.0	6.3	6.4	12.8	0.7	1.5	2.6	4.2	8.7	2.5	0.4	20.2	4.4	6.6	5.5	0.9	7.1	8.7	7.5	0.6
62	3.0	7.3	7.9	15.7	0.8	1.8	3.3	4.9	10.8	2.8	0.6	23.1	4.6	7.8	6.3	1.0	8.8	9.8	8.5	0.6
63	4.0	7.3	7.9	15.7	0.8	1.8	3.3	4.9	10.8	2.8	0.6	23.9	4.9	7.8	6.3	1.0	8.8	9.8	8.5	0.6
72	4.0	8.0	9.5	18.9	0.9	2.4	4.1	6.0	13.0	3.5	0.7	27.6	4.3	9.7	8.5	0.8	10.9	11.0	9.7	0.6
73	6.0	8.0	9.5	18.9	0.9	2.4	4.1	6.0	13.0	3.5	0.7	28.5	4.8	9.7	8.5	0.8	10.9	11.0	9.7	0.6
74	6.0	8.0	9.5	18.9	0.9	2.4	4.1	6.0	13.0	3.5	0.7	29.9	5.7	9.7	8.5	0.8	10.9	11.0	9.7	0.6




Figure 2. Vertically ported

ØU = 4 Holes

J = Key Length

K = Key Width

DuraCirc standard dimensions

Pump Model	A	B	C	D	E	F	G	J	K	L	M	N	P	Q	R	S	T	U	V	X
32	1.0	4.1	5.8	9.9	0.5	0.9	1.7	1.3	0.2	13.0	2.0	4.9	4.0	1.6	6.3	5.1	4.0	0.5	8.0	1.3
33	1.5	4.1	5.8	9.9	0.5	0.9	1.7	1.3	0.2	13.2	2.0	4.9	4.0	1.6	6.3	5.1	4.0	0.5	8.0	1.3
34	2.0	4.1	5.8	9.9	0.5	0.9	1.7	1.3	0.2	13.9	2.4	4.9	4.0	1.6	6.3	5.1	4.0	0.5	8.0	1.3
42	2.0	4.9	6.9	11.8	0.6	1.1	2.2	1.6	0.3	16.3	2.0	5.1	6.1	1.9	8.7	6.3	4.9	0.6	10.0	1.7
43	2.0	4.9	6.9	11.8	0.6	1.1	2.2	1.6	0.3	16.6	2.4	5.1	6.1	1.9	8.7	6.3	4.9	0.6	10.0	1.7
52	2.0	5.9	8.4	14.3	0.7	1.5	2.6	2.5	0.4	18.6	2.4	5.2	7.9	0.7	9.1	7.5	5.9	0.6	12.8	2.2
53	2.5	5.9	8.4	14.3	0.7	1.5	2.6	2.5	0.4	19.1	2.6	5.2	7.9	0.7	9.1	7.5	5.9	0.6	12.8	2.2
54	3.0	6.3	8.4	14.6	0.7	1.5	2.6	2.5	0.4	20.2	3.5	5.2	7.9	0.7	9.1	7.5	5.9	0.6	12.8	2.2
62	3.0	7.3	10.1	17.4	0.7	1.8	3.3	2.8	0.6	23.1	3.3	192	7.9	1.7	10.2	8.7	7.1	0.6	15.6	3.0
63	4.0	7.3	10.1	17.4	0.7	1.8	3.3	2.8	0.6	23.9	3.6	192	7.9	1.7	10.2	8.7	7.1	0.6	15.6	3.0

Pump Model	A	B	C	D	E	F	G	J	K	L	M	N	P	Q	R	S	T	U	V	X
72	4.0	8.0	11.6	19.6	0.8	2.4	4.1	3.5	0.7	27.6	3.8	8.4	10.2	1.2	12.2	9.8	8.3	0.6	18.7	3.5
73	6.0	8.0	11.6	19.6	0.8	2.4	4.1	3.5	0.7	28.5	4.3	8.4	10.2	1.2	12.2	9.8	8.3	0.6	18.7	3.5
74	6.0	8.0	11.6	19.6	0.8	2.4	4.1	3.5	0.7	29.9	5.2	8.4	10.2	1.2	12.2	9.8	8.3	0.6	18.7	3.5

Options

- Silicon Carbide/Silicon Carbide mechanical seal faces.
- Single mechanical shaft seal with flush.
- Double mechanical shaft seal.
- EDPM or FPM O-ring seal, single and flushed.
- Product wetted elastomers in FPM or FFPM.
- High efficiency Hi-Flow rotor.
- Horizontal or vertical porting.
- Heating and cooling jacket.
- Rectangular inlet.
- Aseptic option (see separate data sheet)
- Stainless steel shroud covering coupling and motor.
- Baseplate fitted with adjustable stainless steel ball feet.

Pump sizing

In order to correctly size a circumferential piston pump some essential information is required. Provision of this information listed below enables our Technical Support personnel to obtain the optimum pump selection.

Product/Fluid Data

- Fluid to be pumped
- Viscosity
- Pumping temperature, minimum, normal and maximum
- Cleaning in Place temperature(s), minimum, normal and maximum

Performance Data

- Flow rate, minimum, normal and maximum
- Discharge head/pressure (closest to pump outlet)
- Suction condition

This document and its contents are subject to copyrights and other intellectual property rights owned by Alfa Laval Corporate AB. No part of this document may be copied, re-produced or transmitted in any form or by any means, or for any purpose, without Alfa Laval Corporate AB's prior express written permission. Information and services provided in this document are made as a benefit and service to the user, and no representations or warranties are made about the accuracy or suitability of this information and these services for any purpose. All rights are reserved.

200003946-5-EN-US

© Alfa Laval Corporate AB

How to contact Alfa Laval

Up-to-date Alfa Laval contact details for all countries are always available on our website at www.alfalaval.com