

ROLEC DH INDUCTION SYSTEMS

The simplicity of the ROLEC DH means dry hopping just got safer and easier.



The ROLEC DH units utilize the Ampco SBI pump to safely induce dry hop pellets, fruit, spices coffee and more directly into the stream of beer while recirculating the fermenter.

The systems use carbon dioxide (CO₂) to purge oxygen from the hop chamber.

Pellets and other media can be induced into fermenting, finished or crashed beer.

The chopper pump creates a differential pressure for induction from the vessel.

The pellets and other media is chopped to maximize the surface area, flavor and aroma.



SBI Blender

FEATURES:

- 3 Models DH45/DH90/DH250
- A glass-top manway on the DH90 and DH250 allows the user to ensure the pellets are moving
- Gauges and sight glasses aid the user in monitoring induction and pressures
- Everything needed for pellet induction is contained on the ROLEC DH
- All components are sanitary and CIP-able (no additional CIP pump is required)
- The fully portable DH can be used on many fermenters and fits well in cramped cellars
- Recirculation can be done as long as desired (Ampco recommends 1-4 fermenter turnovers) dependent upon hops to beer ratio
- Improved aroma and flavor profile



Model DH250



Model DH90



Model DH45

NOT JUST FOR HOPS



SPICES

HOPS

COFFEE

TEA

VANILLA

SYRUP


BOURBON

FRUIT


SPECIFICATIONS

| | PELLET CAPACITY | PUMP | RECIRCULATION /MIN | PORT SIZE | MOTOR |
|--------------|-----------------|---------|--------------------------|-------------|--------------|
| DH45 | 44 lbs/20 kg | SBI-R10 | 2.9 bbls/3.4 hectoliters | 1.5"/DIN 40 | 5 hp/4 kW |
| DH90 | 88 lbs/40 kg | SBI-R10 | 2.9 bbls/3.4 hectoliters | 1.5"/DIN 40 | 5 hp/4 kW |
| DH250 | 264 lbs/120 kg | SBI-R20 | 3.7 bbls/4.3 hectoliters | 2"/DIN 50 | 10 hp/7.5 kW |

- Base material 304 stainless steel, wetted parts 316L stainless steel
- All models include variable frequency drive (VFD) for motor control
- Stainless steel casters
- The DH90 and DH250 can CIP with or without a sprayball due to its internal whirlpool system. (Sprayball for the hop chamber is optional)
- The DH45 requires a sprayball for CIP.
- 25'/7m cord standard for DH45, 50'/15m cord standard for DH90 & DH250



Functional design under license of ROLEC PROZESS- UND
BRAUTECHNIK GMBH, GERMANY, United States Patent no. 8,875,616



Recommended fermenter heights

Ampco Pumps
Company

Ampco Pumps Company
2045 W. Mill Road
Glendale, WI 53209 / USA
Tel: 414.643.1852
info@ampcopumps.com

AMPCO 
APPLIED PRODUCTS

Ampco Pumps
GmbH

Ampco Pumps GmbH
Gewerbepark West II 7
76863 Herxheim Germany
Phone: +49 7276 5058515
info@ampcopumps.de